

Standard Range Pulse MDT

Metering Data Transceiver



The Standard Range Pulse MDT records data from meters that generate a pulse output and transmits the totalizer count via radio towards the DCAP every hour. It is compatible with nearly all water, gas and electric utility meters that use a reed switch or a piezoelectric pulse generator.

The Tehama Wireless Standard Range MDTs have an open field range over 3500 feet and is powered by two AA batteries with expected battery life from five to seven years.

The MDT is available either with a single pulse input for single meter usage or dual inputs for co-located hot and cold water meters or other two-meter combinations.

Other variations and features are available such as:

- Top-of-the-hour synchronize Time of Use (ToU) with 15-minute interval data
- Generated Pulse version for older Hersey and newer Zenner meters
- IP-68 rated Submersible version for pit or outdoor installation
- Integrated Remote Display, California approved (See Display MDT Data sheet).

Specifications

Inputs Options	Pulse signal from water, electric, gas, run-time, or BTU meters	
	Hersey/Zenner pulse water meter (generated pulse meters)	
MDT Data Storage	TW-160B-P: Four to five readings max	
	• TW-160xx-PTx: Over 2000 data pts. (28+ days @ 15 Min interval)	
Data Resolution	TW-160B-P/Y: 1-hour interval	
	TW-160X-PT: 15-minute interval, Top of the Hour synchronized	
Max Pulse Rate	• -P: 20 pulses per second, 25mS minimum pulse width	
	• -Y: 25KHz, 40uS minimum pulse width (generated pulse meters only)	
Radio	902 – 928 MHz; FCC and IC Certified	
	Open field range over 3500 feet*	
LED	Indicates on/off and RF network connection status. From button press:	
	Solid Green: good Link Quality	
	Solid Amber: OK Link Quality	
	Red or Flashing: poor Link Quality or syncing to Network	
Operating Envir.	-20 to 145 degrees F, up to 90% RH, non-condensing.	
Power	Two AA Alkaline (standard)	
	Two AA Lithium (Optional, for for sub-freezing temperatures)	
	Sealed primary lithium battery (Submersible)	
Typical Battery	5-7 years @ 50 to 90 deg. F, Reduced at extreme temperatures	
Life	10-12 years @ 40 to 100 deg. F (Submersible)	
Dimensions	4.3" x 2.2" x 1.2" (Regular), 6.2" x 2.4" x 1.5" (Submersible)	

Continual product enhancements may cause specifications to change without notice.

^{*}Actual range may vary depending on installation location and topography.





Models

Battery powered			
Pulse MDT, battery powered	TW-160B-P	Single pulse input counter, one-hour interval data, no on-board memory	
Hersey/Zenner MDT, battery Power.	TW-160B-Y	Single short generated pulse input, typical of Hersey or Zenner meters, one hour interval, no on-board memory	
Pulse MDT, ToU, Battery Powered	TW-160B-PT	Single Pulse input, 15-minute guaranteed (*) Time-of-Use interval data with on-board data memory. Readings are synchronized to the top of the hour for accurate billing	
Multi-input			
Dual Pulse MDT, Battery Power	TW-160B-PP	Dual pulse input counters, one-hour interval data, no on-board memory	
Pulse MDT, Internal Temp, Battery Power	TW-160B-PI	Single Pulse input, Internal temperature, 1-Hr interval data, no on-board memory	
Pulse MDT, ToU, Internal Temp, Battery Power	TW-160B-PTI	Single Pulse input, Internal temp., 15-minute guaranteed (*) Time-of-Use interval data with onboard data memory. Readings are synchronized to the top of the hour for accurate billing	
Submersible MDT, fully potted with sealed 10+year battery			
Submersible MDT, Pulse	TW-167S-P	Single pulse input counter, one-hour interval data. Fully potted for submersible pit meter applications and outdoor environments Separate Data Sheet available on web site	

^{*:} Adequate repeater coverage is required for guaranteed delivery.

Other combinations and sensor inputs are available by special order. Please contact Tehama for details.

Contact us:

Tehama Wireless

2431 5th Street
Berkeley, CA 94710
415.495.7344
info@TehamaWireless.com
www.TehamaWireless.com



©2022 Tehama Wireless Design Group Rev.2207



^{**}Note** Standard and Max Range systems are NOT compatible: only Max Range MDTs must be used with a Max Range Repeater (and Max Range DCAP) and vice versa. Refer to AN-119 in the documents section of our website for more information.